





Titusoft for Drawers

Titusoft WD

Soft Closing System for Wooden Drawer

For wooden drawer with roller runners




		Technical details		Item number		Grey	White
Titusoft WD		Titusoft mechanism	973-0X35 →	380			
		Activator	973-4451 →	380	350		
 Titusoft mechanism							
 Activator							
 250 Pcs 200 Pcs (973-0X35 + activator)		Made of plastic					

Bag of 1 973-0X35-380-K2  120 Bags	
· 1 Titusoft mechanism · 1 activator · 2 screws Ø3.5mm x 20mm · 2 screws Ø3.5mm x 12mm · 1 mounting instruction sheet	
Bag of 2 973-0X35-380-K1  80 Bags	
· 2 Titusoft mechanisms · 2 activators · 4 screws Ø3.5mm x 20mm · 4 screws Ø3.5mm x 12mm · 1 mounting instruction sheet	

- Works with most roller runner drawer slides
- Easy, intuitive mounting
- Smooth, soft closing action independent of drawer hardware
- Optimal closing speed
- Non-handed design


Capacity chart



Mount 1 or 2 Titussoft mechanisms depending on drawer weight and width


Mounting details

1.




Position the Titussoft mechanism on the top of the drawer slide

2.




Fix with 2 screws L=20mm

3.



1. Rest the activator against the drawer front
2. Align the vertical position of the activator with the top of the Titussoft mechanism and mark the screw locations

4.





Fix with 2 screws L=12mm

A trial mounting is always recommended. Please contact Titus Group or your local distributor for further technical assistance.

Titusoft MD

Soft Closing System for Metal Box

For metal boxes



Titusoft MD



Titusoft mechanism



Activator




Mounting jig




250 Pcs
150 Pcs (973-0X39 + activator) Made of plastic

Technical details

Retrofit mounting



Factory mounting (system holes)



Item number

Titusoft mechanism
for factory mounting

973-0X95 →

380

Titusoft mechanism
for retrofit mounting

973-0X39 →

380

309

Activator

973-4125 →

350

Mounting jig

973-4126 →

Bag of 1

973-0X39-380-K2  90 Bags

- 1 Titusoft mechanism
- 1 activator
- 1 mounting jig
- 4 screws
- 1 mounting instruction sheet


Bag of 2

973-0X39-380-K1  60 Bags

- 2 Titusoft mechanisms
- 2 activators
- 1 mounting jig
- 8 screws
- 1 mounting instruction sheet


- One-for-all soft closing for single skin metal boxes
- Allows for easy factory mounting or retrofit application
- Intuitive positioning
- Preserve the life-time of the drawer

Capacity chart




Mounting details

Retrofit mounting



Factory mounting





A trial mounting is always recommended. Please contact Titus Group or your local distributor for further technical assistance.

Titusoft FF

Soft Closing System for Face Frame Cabinets with Wooden Drawer

For wooden drawer
with roller runners




Technical details


Titusoft FF



Titusoft mechanism



Activator



Item number

973-0M99 →

973-4451 →

Grey

380

380

White

350

Bag of 1

973-0M99-380-K1  300 Bags


- 1 Titusoft mechanism
- 1 activator grey
- 2 screws Ø3.5mm x 25mm
- 2 screws Ø3.5mm x 12mm
- 1 mounting instruction sheet



250 Pcs

Made of plastic


- Works with most roller runner drawer slides
- Easy, intuitive mounting
- Smooth, soft closing action independent of drawer hardware
- Non-handed design



Mount 1 or 2 Titusoft mechanisms depending on drawer weight and width


Mounting details

1.




Position the Titusoft on the top of a drawer slide

2.




Screw the Titusoft mechanism to the face frame

3.



Align the activator with the top of the Titusoft mechanism and fix with two screws

4.



Fix with 2 (3) screws L=12mm

A trial mounting is always recommended. Please contact Titus Group or your local distributor for further technical assistance.

